



ROUND SUPPLY GRILLES

RA50/RA54

ALUMINUM

RA50 single deflection round supply grilles are recommended for applications in which one set of individually adjustable blades are required to deflect the supply air in either the horizontal plane or the vertical plane.

RA54 double deflection round supply grilles are recommended for applications in which two sets of individually adjustable blades are required to accommodate any type of room layout or changing job conditions. The blades can be set to allow the air spread to be set left or right and up or down for maximum versatility.

The wide rolled frame is suited for applications in which interior aesthetics clash with standard square and rectangular air outlets. The RA series can be mounted on walls or on ceilings using an optional duct mounting ring. The duct mounting ring leaves no visible fasteners from the room side of the grille.

FEATURES

- Aluminum construction
- Extruded 3/4" blades on 3/4" centers hold position under typical conditions of pressure and velocity
- Rolled margin that is 1-1/2" wide blends in to walls and ceilings and fits with many architectural styles
- Optional duct mounting ring facilitates easy installation
- Standard finish is white (WH) or mill (ML)

Accessories

- Opposed blade damper (DMPR)
- Duct mounting ring (DMR)
- Round butterfly damper (RBD)*
- Round opposed blade damper (ROD)*
- Round radial blade damper (RRD)*
- Equalizing grid (TF)*

*Note: These accessories are ordered separately and ship loose for field installation

Available Sizes (in.)

RA50/RA54

- 6
- 8
- 10
- 12
- 14
- 16
- 18
- 20