


- NOTES:
- MINIMUM 25 VA
NOTE: POWER CONSUMPTION REQUIREMENTS WILL VARY DEPENDING UPON FIELD SUPPLIED/MOUNTED ACCESSORIES.
 - MAXIMUM 10 VA.
 - SUPPLIED, MOUNTED, WIRED AND/OR PIPED BY MFG.
 - LOW TUBING IS BLUE, HIGH IS RED
 - EARTH GROUNDING OF CHASSIS MUST BE PROVIDED BY OTHERS IN THE FIELD. (IF REQUIRED).
 - REFER TO MOTOR WIRING DIAGRAM FOR TRANSFORMER AND FAN RELAY WIRING (IF APPLICABLE).
 - CONNECT CONTROLLER TO THERMOSTAT BETWEEN SA BUS. CONNECTION MAY ALSO BE MADE USING RJ45 JACK.
 - SEE ORDER ACKNOWLEDGEMENT FOR OPTIONAL ITEM REQUIREMENTS.



UNCONTROLLED DOCUMENT WHEN PRINTED

THIS DRAWING MAY NOT REFLECT THE MOST CURRENT REVISION. PLEASE CHECK TO MAKE SURE DRAWING IS CURRENT.

THIS DRAWING CONTAINS PROPRIETARY DATA. UNAUTHORIZED DISCLOSURE REPRODUCTION, OR USE IS STRICTLY PROHIBITED WITHOUT WRITTEN PERMISSION.

TITLE:	MATERIAL:
WD, FAN CONTROLS, FPC-ZEC101 SUBMITTAL	

REVISION DESCRIPTION

REVISED FOR ZEC DESIGN CHANGES (PRESSURE SW,SAT & DAT) AS PER SEQUENCE OF OPERATION

ECR NO.	BY	DATE	CK BY	DATE	DO NOT SCALE DRAWING DIMENSIONS ARE IN INCHES UNLESS OTHERWISE NOTED	SCALE	PART NO.	SHEET	DRAWING NO	REV
3889	SP	03/29/19	AR / JAC	03/29/19		NTS	87-10982 -00		87-10982	01