


STANDARD FEATURES:

1. 22 GAUGE GALVANIZED STEEL CASING CONSTRUCTION
2. 1/2" DUAL DENSITY LINING
3. ROUND INLET COMPATIBLE WITH NOMINAL RIGID AND FLEX DUCT CONNECTIONS
4. SLIP AND DRIVE DISCHARGE CONNECTION
5. PATENTED FLO-CROSS MULTIPOINT FLO SENSOR
6. DAMPER SHAFT WITH DELRIN BEARINGS AND POSITION INDICATOR
7. LOW LEAKAGE DAMPER WITH SEAL
8. ELECTRIC HEAT
9. RIGHT OR LEFT HAND CONFIGURATIONS AVAILABLE (RIGHT HAND SHOWN)



		<p>LINER OPTIONS:</p> <input type="checkbox"/> 1/2" DUAL DENSITY <input type="checkbox"/> 1" DUAL DENSITY <input type="checkbox"/> ENVIROSEAL <input type="checkbox"/> INSULGUARD <input type="checkbox"/> NO LINER	<p>CONSTRUCTION:</p> <input type="checkbox"/> 20 GAUGE	<p>NOTES:</p> <ol style="list-style-type: none"> 1. RECOMMENDED HEAT RISE IS 45 °F OR LESS 2. LEAVING AIR TEMPERATURE (LAT) MAY NOT EXCEED 100 °F. <p>HELPFUL FORMULAS:</p> $KW = \frac{CFM * DT}{3160} \quad DT = \frac{KW * 3160}{CFM}$ <p>LAT = DT + EAT</p>
SIZE	CFM RANGE MIN - MAX	SEE SUBMITTAL SD-7005 FOR LINER PROPERTIES	<p>ACCESSORIES:</p> <input type="checkbox"/> DISC. SWITCH <input type="checkbox"/> DUSTTIGHT SEAL <input type="checkbox"/> HANGER BKT <input type="checkbox"/> FUSING	
24	1800 - 7100			
<p>JOB NAME: _____</p> <p>LOCATION: _____</p> <p>ARCHITECT: _____</p> <p>ENGINEER: _____</p> <p>CONTRACTOR: _____</p>		<p>SUBMITTED BY: _____</p> <p>DATE: OCTOBER '19</p> <p>DRAWING NUMBER: SD-7012</p>		<p>SDV - SINGLE DUCT TERMINAL UNIT</p> <p>HIGH CAPACITY WITH ELECTRIC HEAT</p>