

4 ROW WATER COIL

Cooling/Heating Only
or with Re-Heat coil

DIMENSIONS - In [mm]

See Dwgs.
CCC-001, Figs. 1 & 2
CCC-002, Fig. 5

STANDARD CIRCULATION					
UNIT SIZE	COIL CONNEX	A	B	C	D
08	7/8 [23]	6-7/8 [175]	3-5/8 [92]	4-1/8 [105]	15-3/4 [401]
12					
16					
20	1-1/8 [29]				15-7/8 [404]
30					20-7/8 [531]
40	1-3/8 [35]			4-3/8 [112]	23-1/8 [588]

"LO GPM" CIRCULATION						"HIGH GPM" CIRCULATION						
UNIT SIZE	COIL CONNEX	A	B	C	D	UNIT SIZE	COIL CONNEX	A	B	C	D	
08	7/8 [23]	6-7/8 [175]	3-5/8 [92]	4-1/8 [105]	15-3/4 [401]	08	7/8 [23]	6-7/8 [175]	3-5/8 [92]	4-1/8 [105]	15-3/4 [401]	
12						1-1/8 [29]	20-7/8 [531]					20-5/8 [524]
16												
20	1-1/8 [29]											
30							1-3/8 [35]					
40	1-5/8 [42]											

NOTES:

1. All dimensions are Inches [millimeters].
All dimensions are ±1/2" [13mm].
Metric values are soft conversion.
2. All connections are ODM copper sweat unless otherwise noted.
3. Field piping should be based on job requirements, not unit connection size.

TITLE:

BLOWER COIL UNIT
4 ROW WATER COOLING/HEATING ONLY OR W/RE-HEAT
COIL CONNECTION LOCATION



ENVIRO-TEC®

DRW BY: WRG	DATE: 12/03/19	SCALE: 1=22	DRAWING NO.
CKD BY: TW	DATE: 12/03/19	REV: A	

CCC-020

THIS DRAWING CONTAINS PROPRIETARY DATA.
UNAUTHORIZED DISCLOSURE, REPRODUCTION, OR USE
IS STRICTLY PROHIBITED WITHOUT WRITTEN PERMISSION

DO NOT SCALE DRAWING
DIMENSIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.
CONTACT FACTORY FOR CERTIFIED DRAWINGS.