



INLET VALVE			
DIA.	"A"	"B"	Ø "I"
4"	16-5/8" [422]	13-1/8" [332]	3-7/8" [98]
5"	16-5/8" [422]	13-1/8" [332]	4-7/8" [124]
6"	16-5/8" [422]	13-1/8" [332]	5-7/8" [149]
8"	17-5/8" [448]	12-1/8" [308]	7-7/8" [200]
INDUCED AIR INLET			
--	"C"	"D"	--
--	12" [305]	13" [330]	--

NOTES:

1. All dimensions in Inches [millimeters]. All dimensions ± 1/4" [6mm].
2. Left Hand unit shown, Right Hand unit opposite.
3. 90 degree control enclosure is perpendicular to the unit. Includes (4) knockouts on bottom. Provide sufficient clearance to access electrical controls and comply with applicable codes and ordinances.
4. NEC (36") clearance is straight out from control enclosure.



THIS DRAWING CONTAINS PROPRIETARY DATA. UNAUTHORIZED DISCLOSURE, REPRODUCTION, OR USE IS STRICTLY PROHIBITED WITHOUT WRITTEN PERMISSION.

SUBMITTAL DRAWING
ALL DRAWINGS ARE SUBJECT TO CHANGE WITHOUT PRIOR NOTICE

DO NOT SCALE DRAWING
DIMENSIONS ARE IN INCH [MM] FORMAT +/- 1/8 [3] UNLESS OTHERWISE NOTED

TITLE:

**MODEL CRB07 COOLING ONLY
90 DEGREE ENCLOSURE**

DATE

07/20/20

SHEET

PAGE 1 OF 1

DRAWING NO

10-80086

REV

A