



SPECIFICATIONS

Tri-Flex Return Grilles, Steel

T70, T70D, T80, T80D Suggested Specification:

The steel return grille shall be Tuttle & Bailey model T70 (horizontal bars) or T80 (vertical bars). The grille shall be provided with fixed bars on 3/4" centers. Construction shall be of 22 gauge steel with a 1-1/4" wide margin on all sides with mitered corners. Blade deflection angle shall be available in 0° (T70/T80) or 35° (T70D/T80D). The grille shall be available with countersunk screw holes for a clean, unobtrusive appearance.

Optional volume adjustment damper (Model SOBD) shall be operable from face and constructed of heavy gauge steel.

Finish shall be Tuttle & Bailey White (WH) electrocoat finish. The finish shall be an anodic acrylic paint, baked at 315°F for 30 minutes with a pencil hardness of HB to H.

The manufacturer shall provide published performance data tested in accordance with ANSI/ASHRAE Standard 70-2006 at isothermal conditions.

T75, T75D, T85, T85D Suggested Specification:

The steel return grille shall be Tuttle & Bailey model T75 (horizontal bars) or T85 (vertical bars). The grille shall be provided with fixed bars on 1/2" centers. Construction shall be of 22 gauge steel with a 1-1/4" wide margin on all sides with mitered corners. Blade deflection angle shall be available in 0° (T75/T85) or 35° (T75D/T85D). The grille shall be available with countersunk screw holes for a clean, unobtrusive appearance.

Optional volume adjustment damper (Model SOBD) shall be operable from face and constructed of heavy gauge steel.

Finish shall be Tuttle & Bailey White (WH) electrocoat finish. The finish shall be an anodic acrylic paint, baked at 315°F for 30 minutes with a pencil hardness of HB to H.

The manufacturer shall provide published performance data tested in accordance with ANSI/ASHRAE Standard 70-2006 at isothermal conditions.

