


**STANDARD FEATURES:**

1. 22 GAUGE GALVANIZED STEEL CASING CONSTRUCTION
2. 1/2" DUAL DENSITY LINING
3. ROUND INLET COMPATIBLE WITH NOMINAL RIGID AND FLEX DUCT CONNECTIONS
4. SLIP AND DRIVE DISCHARGE CONNECTION
5. PATENTED FLO-CROSS MULTIPOINT FLO SENSOR
6. DAMPER SHAFT WITH DELRIN BEARINGS AND POSITION INDICATOR
7. LOW LEAKAGE DAMPER WITH SEAL
8. HOT WATER HEAT (SD-7007)
9. INTEGRAL ATTENUATOR
10. RIGHT OR LEFT HAND CONFIGURATIONS AVAILABLE (RIGHT HAND SHOWN)



\*DIM LISTED FOR 1 & 2 ROW COILS,  
ADD 2-1/4" FOR 4 ROW COILS

**LINER OPTIONS:**

- 1/2" DUAL DENSITY
- 1" DUAL DENSITY
- ENVIROSEAL
- INSULGUARD
- NO LINER
- GAL. SHEET METAL LINER

SEE SUBMITTAL SD-7005  
FOR LINER PROPERTIES

**CONSTRUCTION:**

- 20 GAUGE
- ACCESS DOOR
- CAM LATCHES

CAM LATCHES REQUIRE AN ACCESS DOOR

**ACCESSORIES:**

- CONTROL ENCLOSURE
- DISC. SWITCH
- DUSTTIGHT SEAL
- HANGER BKT

**TRANSFORMER**

- 120V / 24V
- 208V / 24V
- 240V / 24V
- 277V / 24V
- 480V / 24V

SIZE	CFM RANGE 0 or MIN - MAX
24	0 or 1420 - 7100

JOB NAME: \_\_\_\_\_  
 LOCATION: \_\_\_\_\_  
 ARCHITECT: \_\_\_\_\_  
 ENGINEER: \_\_\_\_\_  
 CONTRACTOR: \_\_\_\_\_

SUBMITTED BY: \_\_\_\_\_  
 DATE: AUGUST '02  
 DRAWING NUMBER: SD-7014

**SDV - SINGLE DUCT TERMINAL UNIT**  
 HIGH CAPACITY WITH HOT WATER COILS  
 AND INTEGRAL ATTENUATOR