



### UNIT SIZE 1006

FAN MOTOR TAP	LO	MD	HI
HORSEPOWER (HP)	1/10	1/8	1/6
AMPS @ 115 VOLTS	1.8	2.1	2.6
AMPS @ 277 VOLTS	0.65	0.8	0.9




### UNIT SIZE 1011

FAN MOTOR TAP	LO	MD	HI
HORSEPOWER (HP)	1/8	1/5	1/4
AMPS @ 115 VOLTS	3.2	4.1	4.9
AMPS @ 277 VOLTS	1.3	1.6	1.9



### UNIT SIZE 1018

FAN MOTOR TAP	LO	MD	HI
HORSEPOWER (HP)	1/4	1/3	1/2
AMPS @ 115 VOLTS	6.9	7.9	8.8
AMPS @ 277 VOLTS	2.7	3.2	3.6



#### NOTES:

- Each fan curve depicts the actual performance for the relative motor tap without any additional fan balance adjustment. Actual specified capacities which fall below a particular fan curve (LO, MD, or HI) can be obtained by adjustment of the electronic fan speed controller. Selections should only be made in the non-shaded areas. Terminals equipped with a hot water coil or electric heater require the addition of the heater pressure drop and the specified E.S.P. prior to making a fan selection. The minimum external static pressure requirement is shown for each fan assembly. The unit fan should not be energized prior to realizing this minimum external static pressure.
- Terminals with Electric Heat (Model VFR-EH) require a minimum of 0.1" w.g. downstream pressure.



THIS DRAWING CONTAINS PROPRIETARY DATA. UNAUTHORIZED DISCLOSURE, REPRODUCTION, OR USE IS STRICTLY PROHIBITED WITHOUT WRITTEN PERMISSION.

SUBMITTAL DRAWING  
ALL DRAWINGS ARE SUBJECT TO CHANGE  
WITHOUT PRIOR NOTICE

DO NOT SCALE DRAWING  
DIMENSIONS ARE IN INCHES UNLESS  
OTHERWISE NOTED

TITLE:  
FAN PERFORMANCE DATA, VFR SERIES C  
UNIT SIZE 10

DATE  
9/8/08

SHEET  
PAGE 1 OF 1

DRAWING NO  
07-80013

REV  
01