



SPECIFICATIONS

T50SS, T60SS, T54SS, T64SS

T50SS, T60SS Suggested Specification:

Stainless steel single deflection supply grille shall be Tuttle & Bailey model T50SS (horizontal blades) or T60SS (vertical blades). The grille shall have individually adjustable blades on 3/4" centers. Construction shall be of #304 stainless steel with a 1-1/4" wide border on all sides with mitered corners. The grille shall be available with countersunk screw holes for a clean, unobtrusive appearance.

Optional volume adjustment damper (Models SSOBD) shall be operable from face and constructed of heavy gauge stainless steel.

The manufacturer shall provide published performance data tested in accordance with ANSI/ASHRAE Standard 70-1991 at isothermal conditions.

The finish shall be the Tuttle & Bailey Satin Polish (SP).

T54SS, T64SS Suggested Specification:

Stainless steel double deflection supply grille shall be Tuttle & Bailey model T54SS (horizontal front blades) or T64SS (vertical front blades). The grille shall have individually adjustable blades on 3/4" centers. Construction shall be of #304 stainless steel with a 1-1/4" wide border on all sides with mitered corners. The grille shall be available with countersunk screw holes for a clean, unobtrusive appearance.

Optional volume adjustment damper (Models SSOBD) shall be operable from face and constructed of heavy gauge stainless steel.

The manufacturer shall provide published performance data tested in accordance with ANSI/ASHRAE Standard 70-1991 at isothermal conditions.

The finish shall be the Tuttle & Bailey Satin Polish (SP).

Model	Width	Height	Material	Frame Style	Module	Fastening Method	Damper	Finish
T50SS T60SS	4" to 48"	4" to 48"	304 - #304 Stainless Steel 316 - #316 Stainless Steel	SF - Surface Mount LT - Lay-in-T-Bar	None 24x24 48x24	01 - Screw Holes (Countersunk) 02 - No Screw Holes	00 - None SSOBD - Stainless Steel OBD	SP - #3 Satin Polish (Standard) WH - White

Example: T50SS - 38x38 - 304 - SF - None - 01 - SSOBD - SP