




- Constructed of 22 Ga. galvanized steel
- 1/2" thick dual density fiberglass insulation meets requirements NFPA 90A and UL181
- Field adjustable fan speed control and automatic reset thermal cutout
- Easy access to internal components for maintenance via removable bottom panel
- Flo-cross sensor
- 24 volt control transformer and fan interlocking relay
- Induced air inlet attenuator
- Flanged discharge connection on electric reheat coil
- Positive pressure heater air flow switch
- Power and control terminal block
- 80/20 Ni-Cr element
- ETL listed; AHRI certified

Options:

- 20 Ga. galvanized steel construction
- PSC Motor (Standard)
 - 120V 208V/240V 277V
- EON Motor (Available on Unit Size 3 and 6)
 - Manual Controls Remote Controls
 - 120V 208V/240V 277V
- Liners
 - 1/2" dual density fiberglass insulation
 - 1" dual density fiberglass insulation
 - 1/2" Enviroseal
 - 1" Enviroseal
 - 1" Insulguard
- Dust tight control enclosure
- Hangar brackets
- Motor disconnect
- Motor fusing
- SSR controlled proportional heat
 - Fused Non-Fused
- Door interlocking disconnect switch
- Manual reset cutout
- Filter



Dimensions in inches

UNIT SIZE	INLET SIZE	PSC HP	EON HP	A	B	C	D	E	F	G	H	I	J
2	6	1/10	-	21	12	11	4 7/8	5 7/8	7 1/2	5 3/8	15	11	11
3	6	1/4	1/2	21	12	11	4 7/8	5 7/8	7 1/2	5 3/8	15	11	11
3	8	1/4	1/2	32 1/4	12	11	4 7/8	7 7/8	7 1/2	5 3/8	15	11	11
4	8	1/4	-	32 1/4	17	16 1/2	4 7/8	7 7/8	8 7/8	5 3/8	17 3/4	13	14 1/2
4	10	1/4	-	32 1/4	17	16 1/2	4 7/8	9 7/8	8 7/8	7 3/8	17 3/4	13	14 1/2
4	12	1/4	-	32 1/4	17	16 1/2	6 7/8	11 7/8	8 7/8	8 3/8	17 3/4	13	14 1/2
5	10	1/2	-	32 1/4	17	16 1/2	4 7/8	9 7/8	8 7/8	7 3/8	17 3/4	13	14 1/2
5	12	1/2	-	32 1/4	17	16 1/2	6 7/8	11 7/8	8 7/8	8 3/8	17 3/4	13	14 1/2
6	10	3/4	1	32 1/4	17	16 1/5	4 7/8	9 7/8	8 7/8	8 3/4	17 3/4	13	14 1/2
6	12	3/4	1	32 1/4	17	16 1/2	6 7/8	11 7/8	8 7/8	8 3/8	17 3/4	13	14 1/2
6	14	3/4	1	32 1/4	17	16 1/2	6 7/8	13 7/8	8 7/8	8 3/8	17 3/4	13	14 1/2

Job: _____
 Location: _____
 Architect: _____
 Engineer: _____
 Contractor: _____

Tag: _____
 Submitted By: _____
 SD - 2187 Rev: C (03/17)

FPS
Fan-Powered Terminal Unit
Series or Constant
Electric Reheat