


STANDARD FEATURES:

1. 22 GAUGE GALVANIZED STEEL CASING CONSTRUCTION
2. 1/2" DUAL DENSITY LINING
3. ROUND INLET COMPATIBLE WITH NOMINAL RIGID AND FLEX DUCT CONNECTIONS
4. SLIP AND DRIVE DISCHARGE CONNECTION
5. PATENTED FLO-CROSS MULTIPOINT FLO SENSOR
6. DAMPER SHAFT WITH DELRIN BEARINGS AND POSITION INDICATOR
7. LOW LEAKAGE DAMPER WITH SEAL
8. INTEGRAL ATTENUATOR
9. RIGHT OR LEFT HAND CONFIGURATIONS AVAILABLE (RIGHT HAND SHOWN)



UNIT SIZE	CFM RANGE MIN TO MAX	L	H	W	A	D	F	G	LINER OPTIONS:	CONSTRUCTION:	ACCESSORIES:
4	0/45 - 230	39 1/2	8	12	5 3/8	3 7/8	2 1/8	7 1/4	<input type="checkbox"/> 1/2" DUAL DENSITY	<input type="checkbox"/> 20 GAUGE	<input type="checkbox"/> CONTROL ENCLOSURE
5	0/70 - 360	39 1/2	8	12	5 3/8	4 7/8	2 1/8	7 1/4	<input type="checkbox"/> 1" DUAL DENSITY	<input type="checkbox"/> ACCESS DOOR	<input type="checkbox"/> DISC. SWITCH
6	0/100 - 520	39 1/2	8	12	3 3/8	5 7/8	2 1/8	7 1/4	<input type="checkbox"/> ENVIROSEAL	<input type="checkbox"/> CAM LATCHES	<input type="checkbox"/> DUSTTIGHT SEAL
7	0/140 - 710	39 1/2	10	12	3 3/8	6 7/8	1 1/8	7 1/4	<input type="checkbox"/> INSULGUARD	CAM LATCHES REQUIRE AN ACCESS DOOR	<input type="checkbox"/> HANGER BKT
8	0/185 - 925	39 1/2	10	12	3 3/8	7 7/8	1 1/8	7 1/4	<input type="checkbox"/> NO LINER		<input type="checkbox"/> TRANSFORMER
10	0/290 - 1450	39 1/2	12 1/2	14	3 3/8	9 7/8	-	5 1/4	<input type="checkbox"/> GAL. SHEET METAL LINER		<input type="checkbox"/> 120V / 24V
12	0/420 - 2100	39 1/2	15	16	3 3/8	11 7/8	-	5 1/4	SEE SUBMITTAL SD-7005 FOR LINER PROPERTIES		<input type="checkbox"/> 208V / 24V
14	0/580 - 2900	39 1/2	17 1/2	20	3 3/8	13 7/8	-	3 1/4			<input type="checkbox"/> 240V / 24V
16	0/740 - 3700	39 1/2	18	24	3 3/8	15 7/8	-	3 1/4			<input type="checkbox"/> 277V / 24V
											<input type="checkbox"/> 480V / 24V

JOB NAME: _____	SUBMITTED BY: _____	SDV - SINGLE DUCT TERMINAL UNIT WITH INTEGRAL ATTENUATOR
LOCATION: _____	DATE: AUGUST '02	
ARCHITECT: _____	DRAWING NUMBER: SD-7002	
ENGINEER: _____		
CONTRACTOR: _____		