


NOTES:

1. COLD DUCT DAMPER FAILS NORMALLY OPEN.
HOT DUCT DAMPER FAILS NORMALLY OPEN.
2. MAIN AIR SUPPLY CONSUMPTION IS 0.033 SCFM.
3. PART NUMBER DEPENDENT ON UNIT SIZE.

ITEM	PART NO	DESCRIPTION
1	10065001	KMC CONTROLLER CSC-3011
2	10058501	KMC DAMPER ACTUATOR MCP-8031
3	NOTE 3	FLO-CROSS SENSOR

JOB NAME: _____ LOCATION: _____ ARCHITECT: _____ ENGINEER: _____ CONTRACTOR: _____	SUBMITTED BY: _____	REV LEVEL: A DATE: 9/01	DWG NO: 1454
DDV/DSV DUAL DUCT VAV PNEUMATIC CONTROLS - Reverse Acting N.O. Cold, N.O. Hot Mixing			

CONTROL DIAGRAM



SEQUENCE OF OPERATION

- 1.) Hot duct air flow is at maximum and cold duct air flow is at zero when the thermostat branch pressure is at 8 PSIG or greater. On a rise in room temperature the thermostat branch pressure will decrease and hot duct air flow will reduce to 0 and the cold duct air flow increases to maximum at 3 PSIG or less. The reverse will occur with a drop in room temperature.
- 2.) The hot duct damper fails open and the cold damper fails open with loss of pneumatic air.